


compact cylinder ADNGF-80-30-P-A

Part number: 554281

FESTO

According to ISO 21287, with plain-bearing guide, piston rod secured against rotation by means of guide rods and yoke plate.



Data sheet

Feature	Value
Stroke	30 mm
Piston diameter	80 mm
Based on the standard	ISO 21287
Cushioning	P: Flexible cushioning rings/plates at both ends
Assembly position	Any
Design structure	Piston Piston rod Profile barrel
Position detection	For proximity sensor
Protection against torque/guide	Guide rod with yoke
Operating pressure MPa	0.1 ... 1 MPa
Operating pressure	1 ... 10 bar
Mode of operation	double-acting
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (subsequently required for further operation)
Corrosion resistance classification CRC	2 - Moderate corrosion stress
PWIS conformity	VDMA24364-B1/B2-L
Ambient temperature	-20 ... 80 °C
Impact energy in end positions	1.8 J
Theoretical force at 0.6 MPa (6 bar, 87 psi), retracting	2,827 N
Theoretical force at 0.6 MPa (6 bar, 87 psi), advance	3,016 N
Moving mass with 0 mm stroke	778 g
Additional mass factor per 10 mm of stroke	43 g
Basic weight for 0 mm stroke	1,468 g
Additional weight per 10 mm stroke	97 g
Pneumatic connection	G1/8
Materials note	Conforms to RoHS
Material of flange screw	Steel
Material cover	Die-cast aluminium, coated
Material seals	TPE-U(PUR)
Material end plate	Anodised wrought aluminium alloy
Material piston rod	High alloy steel
Material cylinder barrel	Smooth-anodised wrought aluminium alloy