

Round cylinder DSNU-5/8"" - -P-A-S2

Part number: 548513

FESTO



Data sheet

Feature	Value
Stroke	0,4 in...8 in
Piston diameter	5/8" "
Piston rod thread	10-32 UNF-2A
Based on standard	ISO 6432
Cushioning	Elastic cushioning rings/plates at both ends
Mounting position	optional
Piston-rod end	Male thread
Design	Piston Piston rod
Position detection	Via proximity switch
Variants	Through piston rod
Operating pressure	0.1 MPa...1 MPa 1 bar...10 bar
Mode of operation	Double-acting
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-4 °F...176 °F
Impact energy in end positions	0,111 ft-lbf
Theoretical force at 0.6 MPa (6 bar, 87 psi), return stroke	20,7 lbf
Theoretical force at 0.6 MPa (6 bar, 87 psi), advance stroke	24,1 lbf
Moving mass for 0 mm stroke	652 oz
Additional weight per 10 mm stroke	57,1 oz
Type of mounting	With accessories
Pneumatic connection	10-32 UNF-2B
Note on materials	RoHS-compliant
Material cover	Wrought aluminium alloy
Material seals	NBR TPE-U(PU)
Material piston rod	High-alloy stainless steel

Feature	Value
Material cylinder barrel	High-alloy stainless steel