


Bus interface CECX-F-PB-S-V0

Part number: 552102
Product to be discontinued

for the CECX and CMXR.

Type to be discontinued. Available until 2017. See Support Portal for alternative products.

FESTO



Data sheet

Feature	Value
Corrosion resistance classification CRC	0
Authorisation	c UL us - Listed (OL)
Materials note	Contains PWIS substances Conforms to RoHS
Power consumption 5 V	1.4 W
Ambient temperature	5 ... 55 °C
Storage temperature	-40 ... 70 °C
Relative air humidity	10 - 95 %
Protection class	IP20
Safety class	III
Product weight	140 g
Test for insensitivity to vibration	EN 60068-2-6-FC 5 - 9 Hz 3,5 mm 9 - 150 Hz 1g
Test for insensitivity to shock	EN 60068-2-27 EA 15 g, 11 ms (half sine)
Status displays	LED (status) LED red = bus fault
Fieldbus interface	Profibus-Slave DP-V0
Fieldbus interface, connection technology	Socket Sub-D 9-pin
Fieldbus interface, transmission rate	9.6 kbit/s up to 12 mbit/s
Fieldbus interface, electrical isolation	Yes
CE mark (see declaration of conformity)	to EU directive for EMC