


axial kit EAMM-A-S95-100A

Part number: 558169

FESTO

Suitable for electric drives.



Data sheet

Feature	Value
Assembly position	Any
Storage temperature	-25 ... 60 °C
Relative air humidity	0 - 95 %
Protection class	IP40
Ambient temperature	-10 ... 60 °C
Transferable torque	60 Nm
Product weight	4,910 g
Interface code, actuator	S95
Interface code, motor in	100A
Materials note	Conforms to RoHS