



# Cantilever axis EGSA-60-100

Part number: 558200

FESTO

For highly dynamic positioning.



## Data sheet

Feature	Value
Working stroke	100 mm
Size	60
Stroke reserve	13 mm
Reversing backlash	$\leq 20 \mu\text{m}$
Spindle diameter	12.7 mm
Spindle pitch	25.4 mm/U
Assembly position	Any
Guide	Recirculating ball bearing guide
Design structure	Electromechanical Cantilever axis
Motor type	Stepper motor Servomotor
Referencing	Reference switch
Spindle type	Ball screw spindle
Max. acceleration	15 m/s <sup>2</sup>
Max. speed	1.5 m/s
Repetition accuracy	$\pm 0,01 \text{ mm}$
Corrosion resistance classification CRC	0
Sound pressure level	$< 62 \text{ dB(A)}$
Protection class	IP20
Ambient temperature	10 ... 40 °C
Deflection depending on the load and projection	Diagram
Max. drive torque	8.3 Nm
Max. force F <sub>x</sub> on projection	1,960 N
Max. force F <sub>y</sub> on projection	200 N
Max. force F <sub>z</sub> on projection	200 N
Max. moment M <sub>x</sub> on projection	25 Nm
Max. moment M <sub>y</sub> on projection	70 Nm
Max. moment M <sub>z</sub> on projection	70 Nm
Max. radial force at drive shaft	110 N
Max. feed force F <sub>x</sub>	200 N
No-load driving torque	0.1 Nm
Reference value for working load, horizontal	10 kg
Reference value for working load, vertical	6 kg
Mass moment of inertia J <sub>L</sub> per kg of working load	0.00164 kgcm <sup>2</sup>
Mass moment of inertia, JO	0.00219 kgcm <sup>2</sup>
Feed constant	25.4 mm/U
Moving mass	1,350 g
Product weight	3,300 g
Mounting type	Internal thread and centring sleeve
Material information, end cap	Wrought Aluminium alloy Anodised
Material information, profile	Wrought Aluminium alloy Anodised
Materials note	Conforms to RoHS

Feature	Value
Material information, drive unit cover	Wrought Aluminium alloy Anodised
Material information, guide rail	Roller bearing steel
Materials information, housing	Wrought Aluminium alloy Anodised
Material information, rotor	Wrought Aluminium alloy Anodised
Material information, slide unit	Wrought Aluminium alloy Anodised
Material information, spindle	Steel