

Flow sensor SFAB-50U-WQ6-2SV-M12

Part number: 565392

FESTO



Data sheet

Feature	Value
Approval	RCM trademark c UL us - Recognized (OL)
CE mark (see declaration of conformity)	To EU EMC Directive In accordance with EU RoHS Directive
CE marking (see declaration of conformity)	To UK instructions for EMC To UK RoHS instructions
Certificate issuing authority	UL E322346
Note on materials	RoHS-compliant
Measured variable	Volume Volumetric flow rate
Flow direction	Unidirectional P1 -> P2
Measuring principle	Thermal
Measurement method	Heat Loss
Start value for flow rate measuring range	0.5 l/min
End value for flow rate measuring range	50 l/min
Operating pressure	0 MPa...1 MPa 0 bar...10 bar
Operating medium	Compressed air to ISO 8573-1:2010 [6:4:4] Nitrogen
Media temperature	0 °C...50 °C
Ambient temperature	0 °C...50 °C
Nominal temperature	23 °C
Accuracy of flow rate	± (3% o.m.v. + 0.3% FS)
Repetition accuracy offset in ± %FS	0.2 %FS
Repetition accuracy span in ± %FS	0.8 %FS
Temperature coefficient span in ± %FS/K	Typ. 0.1%FS/K
Pressure influence span in ± %FS/bar	0.5 %FS/b.
Switching output	2 x PNP or 2 x NPN, switchable
Switching function	Window comparator Threshold value comparator
Switching element function	N/C or N/O contact, switchable
Max. output current	100 mA
Analogue output	0 - 10 V

Feature	Value
Flow characteristic curve start value	0 l/min
Flow characteristic curve end value	50 l/min
Output characteristic curve start value	0 V
Output characteristic curve end value	10 V
Min. load resistance voltage output	10 kOhm
Short circuit current rating	yes
Overload protection	Available
Operational voltage range DC	15 V...30 V
No-load supply current	120 mA
Reverse polarity protection	For all electrical connections
Electrical connection 1, connection type	Plugs
Electrical connection 1, connector system	M12x1, A-coded to EN 61076-2-101
Electrical connection 1, number of connections/cores	5
Type of mounting	With through-hole With H-rail Via wall/surface bracket
Mounting position	optional
Pneumatic connection	For tubing O.D. 6 mm
Product weight	160 g
Material housing	PA-reinforced
Display type	Illuminated LCD, multi-colour
Displayable units	l l/h l/min m3 scf scfm
Setting options	Teach-in Via display and keys
Protection against tampering	PIN code
Degree of protection	IP65
Pressure drop	100 mbar
Protection class	III
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L