


axial kit EAMM-A-E48-52C

Part number: 556995

FESTO

Suitable for electric drives.



Data sheet

| Feature | Value |
|--------------------------|------------------|
| Assembly position | Any |
| Storage temperature | -25 ... 60 °C |
| Relative air humidity | 0 - 95 % |
| Protection class | IP40 |
| Ambient temperature | -10 ... 60 °C |
| Transferable torque | 17 Nm |
| Product weight | 1,210 g |
| Interface code, actuator | E48A E48B |
| Interface code, motor in | 52C |
| Materials note | Conforms to RoHS |