



parallel gripper HGPT-63-A-B-G2

Part number: 560230

FESTO

sturdy, with gripping force retention when closing ...G2.



Data sheet

| Feature | Value |
|--|---|
| Size | 63 |
| Stroke per gripper jaw | 16 mm |
| Max. replacement accuracy | ≤ 0.2 mm |
| Max. angular gripper jaw backlash ax,ay | ≤ 0.1 deg |
| Max. gripper jaw backlash Sz | ≤ 0.02 mm |
| Rotationally symmetrical | ≤ 0.2 mm |
| Repetition accuracy, gripper | ≤ 0.05 mm |
| Number of gripper fingers | 2 |
| Drive system | pneumatic |
| Assembly position | Any |
| Mode of operation | double-acting |
| Gripper function | Parallel |
| Gripper force back-up | On closing |
| Design structure | Inclined plane guided motion sequence |
| Position detection | For proximity sensor |
| Operating pressure | 4 ... 8 bar |
| Operating pressure, sealing air | 0 ... 0.5 bar |
| Max. operating frequency of gripper | ≤ 2 Hz |
| Min. opening time at 0.6 MPa (6 bar, 87 psi) | 294 ms |
| Min. closing time at 0.6 MPa (6 bar, 87 psi) | 185 ms |
| Max. mass per external gripper finger | 1,260 g |
| Operating medium | Compressed air in accordance with ISO8573-1:2010 [7:4:4] |
| Note on operating and pilot medium | Lubricated operation possible (subsequently required for further operation) |
| Corrosion resistance classification CRC | 2 - Moderate corrosion stress |
| PWIS conformity | VDMA24364-B1/B2-L |
| Protection class | IP40 |
| Ambient temperature | 5 ... 60 °C |
| Mass moment of inertia | 93.034 kgcm ² |
| Max. force on gripper jaw Fz static | 5,000 N |
| Max. torque at gripper Mx static | 160 Nm |
| Max. torque at gripper My static | 180 Nm |
| Max. torque at gripper Mz static | 140 Nm |
| Lubrication interval for guide components | 5 Mio SP |
| Product weight | 3,562 g |
| Mounting type | Internal thread and centring sleeve With through-hole and centring sleeve With through-hole and dowel pin With internal thread and dowel pin Optional |
| Pneumatic connection, sealing air | M5 |
| Pneumatic connection | G1/8 |
| Materials note | Conforms to RoHS |
| Material cover cap | High alloy steel, non-corrosive |
| Material housing | Anodised aluminium |
| Material gripper jaws | Steel, hardened |