


# Axial kit EAMM-A-P8-38A-40A

Part number: 562652

FESTO



## Data sheet

| Feature                        | Value          |
|--------------------------------|----------------|
| Mounting position              | optional       |
| LABS (PWIS) conformity         | VDMA24364-B2-L |
| Storage temperature            | -25 °C...60 °C |
| Relative air humidity          | 0 - 95%        |
| Degree of protection           | IP40           |
| Ambient temperature            | -10 °C...60 °C |
| Transmittable torque           | 6.5 Nm         |
| Product weight                 | 100 g          |
| Interface code, actuator       | P8-38A         |
| Interface code, motor in       | 40A            |
| Interface code, clutch housing | 38A.2          |
| Note on materials              | RoHS-compliant |