


manifold rail

VABM-L1-...

Part number: 573605

FESTO



Data sheet

Overall data sheet – Individual values depend upon your configuration.

Feature	Value
Grid dimension	10.5 mm 16 mm 19 mm
Assembly position	Any
Max. number of valve positions	24
Authorisation	c UL us - Recognized (OL)
Corrosion resistance classification CRC	2 - Moderate corrosion stress
PWIS conformity	VDMA24364-B1/B2-L
RSBP classification to CD-0033	F1a
Cleanroom class	ISO class 6
Storage temperature	-20 ... 60 °C
Auxiliary pilot air port 12/14	M5
Pilot exhaust port 82/84	M5
Pneumatic connection, port 1	G1/8 G1/4 G3/8
Pneumatic connection, port 2	M5 M7 G1/8 G1/4
Materials note	Conforms to RoHS
Material manifold	Wrought Aluminium alloy