

# Semi-rotary drive DRRD-63-

Part number: 574407

FESTO



## Data sheet

Feature	Value
Size	63
Swivel angle	180 deg
Cushioning	Internal hydraulic cushioning hard External hydraulic cushioning Internal hydraulic cushioning normal
Mounting position	optional
Design	Rack and pinion
Max. number of intermediate positions	1
Position detection	Via proximity switch
Operating pressure	0.2 MPa...1 MPa 2 bar...10 bar
Mode of operation	Double-acting
CE mark (see declaration of conformity)	To EU Explosion Protection Directive (ATEX)
CE marking (see declaration of conformity)	To UK EX instructions
Explosion protection certification outside the EU	EPL Db (GB) EPL Gb (GB)
Explosion protection	Zone 1 (ATEX) Zone 1 (UKEX) Zone 2 (ATEX) Zone 21 (ATEX) Zone 21 (UKEX) Zone 22 (ATEX)
ATEX category gas	II 2G
ATEX category dust	II 2D
Explosion ignition protection type for gas	Ex h IIC T4 Gb
Explosion ignition protection type for dust	Ex h IIIC T120°C Db
Explosion ambient temperature	-10°C ≤ Ta ≤ +60°C
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)
LABS (PWIS) conformity	VDMA24364 zone III
Ambient temperature	-10 °C...60 °C
Theoretical torque at 0.6 MPa (6 bar, 87 psi)	112 Nm
Permissible mass moment of inertia	4 kgm <sup>2</sup> ...42 kgm <sup>2</sup>

Feature	Value
Type of mounting	Either: With through-hole Via female thread
Pneumatic connection	G3/8
Note on materials	RoHS-compliant
Material drive shaft	Tempered steel
Material cover	Aluminium Anodised
Material seals	NBR TPE-U(PU)
Material housing	Wrought aluminium alloy Smooth anodised