

Mini slide DGSL-20-10-EA

Part number: 570195

FESTO



Data sheet

Feature	Value
Stroke	10 mm
Adjustable end position range/length front	6.5 mm
Adjustable end position range/length rear	5.5 mm
Piston diameter	25 mm
Operating mode, drive unit	Yoke
Cushioning	Short elastic cushioning rings/pads at both ends
Mounting position	optional
Guide	Ball bearing cage guide
Design	Yoke Piston Piston rod Slide
Position detection	Via proximity switch
Operating pressure	0.1 MPa...0.8 MPa 1 bar...8 bar
Max. speed	0.8 m/s
Repetition accuracy	0.3 mm
Mode of operation	Double-acting
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)
Corrosion resistance class CRC	0 - No corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	0 °C...60 °C
Impact energy in end positions	0,45 Nm
Cushioning length	1.2 mm
Max. force F _y	2911 N
Max. force F _z	2911 N
Max. moment M _x	60 Nm
Max. moment M _y	30 Nm
Max. moment M _z	30 Nm
Theoretical force at 0.6 MPa (6 bar, 87 psi), return stroke	247 N
Theoretical force at 0.6 MPa (6 bar, 87 psi), advance stroke	295 N

Feature	Value
Moving mass	660 g
Product weight	1597 g
alternative connections	See product drawing
Type of mounting	With through-hole
Pneumatic connection	G1/8
Note on materials	RoHS-compliant
Material cover	Wrought aluminium alloy
Material seals	HNBR
Material housing	Wrought aluminium alloy
Material piston rod	High-alloy stainless steel