


# Manifold assembly VTUG-S

Part number: 572230

FESTO



## Data sheet

Feature	Value
Electrical control	Individual connection
Electrical I/O system	no
Terminal type	26
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]
Pilot medium	Compressed air to ISO 8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)
Media temperature	-5 °C...60 °C
Ambient temperature	-5 °C...60 °C
Restrictions for environmental and media temperature	-5 ... 50° C Without holding current reduction
Degree of protection	IP40 IP65
Corrosion resistance class CRC	2 - Moderate corrosion stress
Operating pressure	-0.09 MPa...0.1 MPa -0.9 bar...10 bar
Pilot pressure	0.15 MPa...0.8 MPa 1.5 bar...8 bar
Operating pressure for valve terminal with internal pilot air supply	0.15 MPa...0.8 MPa 1.5 bar...8 bar
LABS (PWIS) conformity	VDMA24364-B2-L
CE mark (see declaration of conformity)	To EU EMC Directive
CE marking (see declaration of conformity)	To UK instructions for EMC
Approval	RCM trademark c UL us - Recognized (OL)
Note on materials	RoHS-compliant
Material seals	HNBR NBR
Valve terminal structure	Fixed grid
Max. number of valve positions	16
Max. number of pressure zones	9
Type of actuation	Electric

Feature	Value
Valve function	2x3/2-way, monostable, closed 2x3/2-way, open, monostable 2x3/2-way, open/closed, monostable 5/2 double solenoid 5/2-way, monostable 5/3-way, pressurised 5/3 exhausted 5/3 closed
Design	Piston gate valve
Sealing principle	Soft
Valve size	10 mm 14 mm 18 mm
Pilot air supply	External Internal
Max. standard nominal flow rate	380 l/min at 10 mm 780 l/min at 14 mm 1380 l/min at 18 mm
Exhaust-air function	With flow control option
pneumatic working port	M3 M5 M7 G1/8 G1/4 QS-3 QS-4 QS-6 QS-8 QS-10 QS-5/32 QS-1/8 QS-3/16 QS-1/4 QS-5/16 QS-3/8
Signal status display	LED
Permissible voltage fluctuations	+/- 10 %