


input module

CPX-L-16DE-16-KL-3POL

Part number: 572606

FESTO



Data sheet

Feature	Value
Dimensions W x L x H	(including interlinking block) 50 mm x 107 mm x 41 mm
Product weight	167 g
Ambient temperature	-5 ... 50 °C
Storage temperature	-20 ... 70 °C
Protection class	IP20
Corrosion resistance classification CRC	1 - Low corrosion stress (when installed)
PWIS conformity	VDMA24364-B2-L
Authorisation	c UL us - Listed (OL)
Materials note	Conforms to RoHS
Material housing	PA-reinforced
LED displays	1 group diagnostics 16 channel status
Diagnosis	Short circuit/overload per channel
Parameters configuring	Input debounce time Signal extension time Behaviour after short circuit Module monitoring
Operating voltage range DC	18 ... 30 V
Nominal operating voltage DC	24 V
Intrinsic current consumption at operating voltage	Typically 15 mA
No. of inputs	16
Input characteristics	IEC1131-T2, Typ 01
Switching level	Signal 0: ≤ 5 V Signal 1: ≥ 15 V
Input circuit logic	PNP (positive-switching)
Input debounce time	3 ms (0.1 ms, 10 ms, 20 ms, parameterisable)
Max. residual current inputs per module	1.8 A
Electrical isolation channel – channel	No
Electrical isolation channel – internal bus	No
Protection (short circuit)	Internal electronic fuse protection per module