


connecting cable NEBV-

Part number: 8003577

FESTO



Exemplary representation

Data sheet

Overall data sheet – Individual values depend upon your configuration.

Feature	Value
Additional functions	Reduction of holding current Protective circuit
Cable identification	Without inscription label holder
Connection frequency	50
Electrical connection 1, function	Field device side
Electrical connection 1, design	Angular
Electrical connection 1, connection type	Plug socket Socket, slim
Electrical connection 1, cable outlet	Straight Angled
Electrical connection 1, connection technology	Connection pattern ZC, self-tapping screw Connection pattern ZC, metric screw Plug pattern type C to EN 175301-803 Sub-D
Electrical connection 1, number of pins/wires	2 25 4 44
Electrical connection 2, function	Controller side
Electrical connection 2, design	Angular Round
Electrical connection 2, connection type	Cable Plug
Electrical connection 2, cable outlet	Straight Angled
Electrical connection 2, connection technology	Connection pattern ZB, self-tapping screw M8x1, A-coded to EN 61076-2-104 Open end
Electrical connection 2, number of pins/wires	2 25 3 44
Operating voltage range DC	0 ... 230 V
Operating voltage range AC	0 ... 230 V
Cable length	0.5 ... 30 m
Cable attribute	Standard Suitable for energy chains
Test conditions of cable	Test conditions on request
CE mark (see declaration of conformity)	to EU directive for EMC to EU directive low-voltage devices in accordance with EU RoHS directive
UKCA marking (see declaration of conformity)	To UK instructions for electrical equipment To UK instructions for EMC To UK RoHS instructions

Feature	Value
PWIS conformity	VDMA24364-B2-L
Materials note	Conforms to RoHS
Material cable sheath	PVC TPE-U(PUR)
Cable sheath colour	Grey