


handling module EHMZ-EGSL-35-BS-KF- -

Part number: 8004628

FESTO



Data sheet

Overall data sheet – Individual values depend upon your configuration.

Feature	Value
Working stroke	50 mm
Spindle diameter	8 mm
Spindle pitch	8 mm/U
Assembly position	Vertical
Design structure	Electromechanical linear module With spindle
Position detection	For proximity sensor
Max. acceleration	25 m/s ²
Max. speed	0.5 m/s
Repetition accuracy	±0,015 mm
Duty cycle	100 %
PWIS conformity	VDMA24364 zone III
Storage temperature	-20 ... 60 °C
Relative air humidity	0 - 90 %
Protection class	IP40
Ambient temperature	5 ... 45 °C
Max. feed force F _x	75 N
Feed constant	8 mm/U
Materials note	Conforms to RoHS