

# Electric drive ESBF-BS-63-400-10P

Part number: 574099

FESTO



## Data sheet

Feature	Value
Size	63
Stroke	400 mm
Piston rod thread	M16x1.5
Reversing backlash theoretical	30 µm
Spindle diameter	25 mm
Spindle pitch	10 mm/U
Torsional backlash at piston rod +/-	0.4 deg
Based on standard	ISO 15552
Mounting position	optional
Piston-rod end	Male thread
Type of motor	Servo motor
Position detection	Via proximity switch
Design	Electric cylinder with ball screw
Spindle type	Ball screw
Protection against torque/guide	With plain-bearing guide
Max. acceleration	15 m/s <sup>2</sup>
Max. speed	0.53 m/s
Repetition accuracy	±0.01 mm
Duty cycle	100%
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364 zone III
Storage temperature	-20 °C...60 °C
Suitable for use with food	See supplementary material information
Relative air humidity	0 - 95%
Degree of protection	IP40
Ambient temperature	0 °C...60 °C
Max. drive torque	13.1 Nm
Max. radial force at drive shaft	700 N
Max. feed force Fx	7000 N
Frictional torque independent of load	0.45 Nm
Reference value effective load, horizontal	700 kg

<b>Feature</b>	<b>Value</b>
Reference value effective load, vertical	700 kg
Mass moment of inertia JH per metre of stroke	2.8592 kgcm <sup>2</sup>
Mass moment of inertia JL per kg of working load	0.02533 kgcm <sup>2</sup>
Mass moment of inertia JO	0.48631 kgcm <sup>2</sup>
Moving mass for 0 mm stroke	1829 g
Additional moving mass per 10 mm stroke	52 g
Basic weight for 0 mm stroke	3163 g
Additional weight per 10 mm stroke	87 g
Type of mounting	Via female thread Or accessories
Interface code, actuator	D60
Note on materials	RoHS-compliant
Material cover	Cast aluminium, coated
Material piston rod	High-alloy stainless steel
Material screws	Galvanised steel
Material spindle nut	Rolled steel
Material spindle	Rolled steel
Material cylinder barrel	Smooth-anodised wrought aluminium alloy