

Electric drive ESBF-BS-100-200-20P

Part number: 574119

FESTO



Data sheet

Feature	Value
Size	100
Stroke	200 mm
Piston rod thread	M20x1.5
Reversing backlash theoretical	30 µm
Spindle diameter	40 mm
Spindle pitch	20 mm/U
Torsional backlash at piston rod +/-	0.5 deg
Based on standard	ISO 15552
Mounting position	optional
Piston-rod end	Male thread
Type of motor	Servo motor
Position detection	Via proximity switch
Design	Electric cylinder with ball screw
Spindle type	Ball screw
Protection against torque/guide	With plain-bearing guide
Max. acceleration	15 m/s ²
Max. speed	0.65 m/s
Repetition accuracy	±0.01 mm
Duty cycle	100%
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364 zone III
Storage temperature	-20 °C...60 °C
Suitable for use with food	See supplementary material information
Relative air humidity	0 - 95%
Degree of protection	IP40
Ambient temperature	0 °C...60 °C
Max. drive torque	63.7 Nm
Max. radial force at drive shaft	1100 N
Max. feed force F _x	17000 N
Frictional torque independent of load	0.9 Nm
Reference value effective load, horizontal	1700 kg

Feature	Value
Reference value effective load, vertical	1700 kg
Mass moment of inertia JH per metre of stroke	19.31 kgcm ²
Mass moment of inertia JL per kg of working load	0.10132 kgcm ²
Mass moment of inertia JO	5.0504 kgcm ²
Moving mass for 0 mm stroke	8786 g
Additional moving mass per 10 mm stroke	132 g
Basic weight for 0 mm stroke	11123 g
Additional weight per 10 mm stroke	193 g
Type of mounting	Via female thread Or accessories
Interface code, actuator	D100
Note on materials	RoHS-compliant
Material cover	Cast aluminium, coated
Material piston rod	High-alloy stainless steel
Material screws	Galvanised steel
Material spindle nut	Rolled steel
Material spindle	Rolled steel
Material cylinder barrel	Smooth-anodised wrought aluminium alloy