


manifold rail

VABM-L1-18S-G38-3

Part number: 574456
★ Core product range

FESTO



Data sheet

Feature	Value
Grid dimension	19 mm
Max. number of valve positions	16
Operating pressure MPa	-0.09 ... 1 MPa
Operating pressure	-0.9 ... 10 bar
Authorisation	RCM Mark c UL us - Recognized (OL)
Corrosion resistance classification CRC	2 - Moderate corrosion stress
PWIS conformity	VDMA24364-B1/B2-L
Max. tightening torque, H-rail mounting	1.5 Nm
Max. tightening torque, valve mounting	1.18 Nm
Max. tightening torque, wall mounting	3 Nm
Product weight	297 g
Pneumatic connection, port 1	G3/8
Pneumatic connection, port 3	G3/8
Pneumatic connection, port 5	G3/8
Materials note	Conforms to RoHS
Material manifold	Wrought Aluminium alloy