

pressure sensor SPAW-P25R-G14F-2PA-M12

Part number: 8022782

FESTO

For measuring media pressures, pressure measuring range between 0 and +25 bar, pneumatic connection female thread G1/4.



Data sheet

Feature	Value
Authorisation	RCM Mark c UL us - Listed (OL)
CE mark (see declaration of conformity)	to EU directive for EMC in accordance with EU RoHS directive
UKCA marking (see declaration of conformity)	To UK instructions for EMC To UK RoHS instructions
Materials note	Conforms to RoHS
Measured variable	Relative pressure
Measurement method	Thin metal film pressure sensor
Pressure measuring range start value (MPa)	0 MPa
Pressure measuring range, initial value	0 bar
Pressure measuring range start value (psi)	0 psi
Pressure measuring range end value (MPa)	2.5 MPa
Pressure measuring range, final value	25 bar
Pressure measuring range end value (psi)	362.5 psi
Overload pressure	5 MPa 50 bar
Overload pressure (psi)	725 psi
Operating medium	Compressed air in accordance with ISO8573-1:2010 [-:~:] Fluid media Gaseous media
Medium temperature	-20 ... 85 °C
Ambient temperature	0 ... 80 °C
Accuracy, FS	1 %FS
Repetition accuracy in ± %FS	0.15 %FS
Switch output	2xPNP
Switching function	Freely programmable
Switching element function	Switchable
Max. output current	250 mA
Analogue output	4 - 20 mA
Rise time	3 ms
Short circuit strength	Yes
Operating voltage range DC	15 ... 35 V
Polarity protected	for operating voltage
Electrical connection 1, connection type	Plug
Electrical connection 1, connection technology	M12x1, A-coded in accordance with EN 61076-2-101
Electrical connection 1, number of pins/wires	5
Electrical connection 1, type of mounting	Screw lock
Mounting type	with internal (female) thread with accessories
Assembly position	Any
Pneumatic connection	Female thread 1/4
Product weight	230 g

Feature	Value
Material housing	ABS High alloy steel, non-corrosive
Materials in contact with media	High alloy steel, non-corrosive
Type of display	4-place alphanumeric LED display
Unit(s) that can be displayed	MPa bar kPa kg/cm ² psi
Operating status display	Red LED
Setting options	Via display and buttons
Protection against manipulation	PIN-Code
Threshold value setting range	0.5 ... 100 %
Hysteresis setting range	0.5 ... 99.5 %
Protection class	IP65 IP67
Corrosion resistance classification CRC	4 - Very high corrosion stress
PWIS conformity	VDMA24364 zone III