


# solenoid valve

## VUVS-LT25-T32C-MZD-G14-F8-1C1

Part number: 8035198

FESTO



## Data sheet

| Feature                                 | Value  |
|---|--|
| Valve function                          | 2x3/2 closed, monostable   |
| Type of actuation                       | electrical   |
| Valve size                              | 26.5 mm  |
| Standard nominal flow rate              | 1,000 l/min  |
| Operating pressure MPa                  | -0.09 ... 1 MPa  |
| Operating pressure                      | -0.9 ... 10 bar  |
| Design structure                        | Poppet seat  |
| Type of reset                           | mechanical spring  |
| Authorisation                           | c UL us - Recognized (OL)  |
| Protection class                        | IP65<br>with plug socket<br>to IEC 60529   |
| Nominal size                            | 6.9 mm   |
| Exhaust-air function                    | throttleable   |
| Sealing principle                       | soft   |
| Assembly position                       | Any  |
| Manual override                         | detenting<br>Pushing   |
| Type of piloting                        | Piloted  |
| Pilot air supply                        | external   |
| Flow direction                          | non reversible   |
| Overlap                                 | Underlap   |
| Pilot pressure MPa                      | 0.25 ... 1 MPa   |
| Pilot pressure                          | 2.5 ... 10 bar   |
| b value                                 | 0.4  |
| C value                                 | 4.5 l/sbar   |
| Switching time off                      | 25 ms  |
| Switching time on                       | 10 ms  |
| Duty cycle                              | 100 %  |
| Max. positive test pulse with logic 0   | 2,000 µs   |
| Max. negative test pulse with logic 1   | 3,600 µs   |
| Characteristic coil data                | 24 V DC: 3.3 W   |
| Permissible voltage fluctuation         | +/- 10 %   |
| Operating medium                        | Compressed air in accordance with ISO8573-1:2010 [7:4:4]                                       |
| Note on operating and pilot medium      | Lubricated operation possible (subsequently required for further operation)                    |
| Vibration resistance                    | Transport application test at severity level 2 in accordance with FN 942017-4 and EN 60068-2-6 |
| Shock resistance                        | Shock test with severity level 2 in accordance with FN 942017-5 and EN 60068-2-27              |
| Corrosion resistance classification CRC | 2 - Moderate corrosion stress  |
| Medium temperature                      | -5 ... 60 °C   |
| Pilot medium                            | Compressed air in accordance with ISO8573-1:2010 [7:4:4]                                       |
| Ambient temperature                     | -5 ... 60 °C   |
| Product weight                          | 415 g  |
| Electrical connection                   | Plug pattern type C to EN 175301-803   |

| Feature                       | Value   |
|-------------------------------|---|
|                               | to EN 175301-803                                  |
| Mounting type                 | on manifold rail<br>with through hole<br>Optional |
| Scavenging orifice connection | Non-ducted  |
| Pilot exhaust port 82         | M5  |
| Pilot exhaust port 84         | M5  |
| Pilot air port 12             | M5  |
| Pilot air port 14             | M5  |
| Pneumatic connection, port 1  | G1/4  |
| Pneumatic connection, port 2  | G1/4  |
| Pneumatic connection, port 3  | G1/4  |
| Pneumatic connection, port 4  | G1/4  |
| Pneumatic connection, port 5  | G1/4  |
| Materials note                | Conforms to RoHS                                  |
| Material seals                | HNBR<br>NBR<br>TPE-U(PU)                          |
| Material housing              | Aluminium die cast<br>Painted                     |
| Material screws               | Galvanised steel                                  |