


Servo Press Kit YJKP-..

Part number: 8058596

FESTO



Exemplary representation

Data sheet

Overall data sheet – Individual values depend upon your configuration.

Feature	Value
Pressing force	0 ... 17 kN
Working stroke	100 ... 400 mm
Cable length	5 ... 15 m
Scanning frequency	1,000 Hz
Protocol	EtherNet/IP Modbus TCP TCP/IP
Assembly position	Any
Motor type	Servomotor
Max. acceleration	2 m/s ²
Duty cycle	100%
Feed speed	0 ... 250 mm/s
Accuracy, FS	0.25 %FS
Maximum effective load	19.5 ... 95 kg
Ambient temperature	0 ... 40 °C
Storage temperature	-10 ... 60 °C
Protection class	IP20
Relative air humidity	0 - 90 %
Materials note	Contains PWIS substances Conforms to RoHS
Corrosion resistance classification CRC	0 - No corrosion stress