

Compact cylinder ADN-S-16-15-I-P

Part number: 8076403

FESTO



Data sheet

Feature	Value
Stroke	15 mm
Piston diameter	16 mm
Cushioning	Elastic cushioning rings/plates at both ends
Mounting position	optional
Mode of operation	Double-acting
Piston-rod end	Female thread
Design	Piston Piston rod
Variants	Piston rod at one end
Operating pressure	0.1 MPa...1 MPa 1 bar...10 bar
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)
Corrosion resistance class CRC	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Cleanroom class	Class 6 according to ISO 14644-1
Ambient temperature	0 °C...60 °C
Impact energy in end positions	0.1 J
Theoretical force at 0.6 MPa (6 bar, 87 psi), return stroke	90 N
Theoretical force at 0.6 MPa (6 bar, 87 psi), advance stroke	121 N
Moving mass for 0 mm stroke	6 g
Additional moving mass per 10 mm stroke	4 g
Basic weight for 0 mm stroke	32.5 g
Additional weight per 10 mm stroke	18 g
Type of mounting	Either: With through-hole Via female thread With accessories
Pneumatic connection	M5
Note on materials	RoHS-compliant
Material cover	Anodised wrought aluminium alloy
Material dynamic seals	NBR

Feature	Value
Material housing	Anodised wrought aluminium alloy
Material piston rod	High-alloy stainless steel