

# Servo Press Kit YJKP

Part number: 8077950

FESTO



## Data sheet

Feature	Value
Pressing force	0 ... 17 kN
Working stroke	100 ... 400 mm
Cable length	5 ... 15 m
Scanning frequency	1,000 Hz
Protocol	EtherNet/IP Modbus TCP OPC-UA PROFINET IO TCP/IP
Assembly position	Any
Motor type	Servomotor
Max. acceleration	2 m/s <sup>2</sup>
Duty cycle	100 %
Feed speed	0 ... 250 mm/s
Accuracy, FS	0.25 %FS
Maximum effective load	19.5 ... 95 kg
Product weight	5.5 ... 66.7 kg
Ambient temperature	0 ... 40 °C
Storage temperature	-10 ... 60 °C
Protection class	IP20
Relative air humidity	0 - 90 %
Materials note	Conforms to RoHS
Corrosion resistance classification CRC	0 - No corrosion stress
PWIS conformity	VDMA24364 zone III