

# Mini slide DGST-25-200-PA

Part number: 8085158

FESTO



## Data sheet

Feature	Value
Stroke	200 mm
Adjustable end position range/length front	47 mm
Adjustable end position range/length rear	45.4 mm
Piston diameter	25 mm
Operating mode, drive unit	Yoke
Cushioning	Elastic cushioning rings/plates at both ends
Mounting position	optional
Guide	Ball bearing cage guide
Design	Twin piston Yoke Piston rod Slide
Position detection	Via proximity switch
Operating pressure	0.1 MPa...0.8 MPa 1 bar...8 bar 14.5 psi...116 psi
Max. speed	0.8 m/s
Repetition accuracy	≤ 0.3 mm
Mode of operation	Double-acting
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)
Corrosion resistance class CRC	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-10 °C...60 °C
Impact energy in end positions	0.45 J
Cushioning length	1.2 mm
Max. force F <sub>y</sub>	1170 N
Max. force F <sub>z</sub>	1170 N
Max. moment M <sub>x</sub>	20 Nm
Max. moment M <sub>y</sub>	17 Nm
Max. moment M <sub>z</sub>	17 Nm

<b>Feature</b>	<b>Value</b>
Theoretical force at 0.6 MPa (6 bar, 87 psi), return stroke	495 N
Theoretical force at 0.6 MPa (6 bar, 87 psi), advance stroke	589 N
Moving mass	2418.5 g
Product weight	5076 g
Type of mounting	With through-hole
Pneumatic connection	G1/8
Note on materials	RoHS-compliant
Material cover	Wrought aluminium alloy
Material seals	HNBR
Material guide	POM TPE-E High-alloy steel
Material housing	Wrought aluminium alloy
Material piston rod	High-alloy stainless steel