

# PROFINET Interface CPX-AP-I-PN-M12

Part number: 8086607

FESTO



## Data sheet

Feature	Value
Dimensions (W x L x H)	45 x 170 x 35 mm
Type of mounting	On H-rail via accessories With through-hole
Max. number of modules	80
Product weight	186 g
Ambient temperature	-20 °C...50 °C
Storage temperature	-40 °C...70 °C
Relative air humidity	5 - 95% Non-condensing
Degree of protection	IP65 IP67
Note on degree of protection	Unused connections sealed
Corrosion resistance class CRC	1 - Low corrosion stress
Max. cable length	50 m system communication
Note on max. cable length	Power supply according to nominal voltage
LABS (PWIS) conformity	VDMA24364-B2-L
CE mark (see declaration of conformity)	To EU EMC Directive
CE marking (see declaration of conformity)	To UK instructions for EMC
KC mark	KC-EMV
Approval	RCM trademark c UL us listed (OL)
Certificate issuing authority	UL E239998
Note on materials	RoHS-compliant
Material housing	PA PC Die-cast zinc, nickel-plated
Material o-ring	FPM
Diagnostics via LED	Diagnostics per module Network fault Power supply, electronics/sensors Load power supply System diagnostics Service required

Feature	Value
Diagnostics via bus	APDD invalid Load switch-off Communication with AP module interrupted Electronics/sensors overvoltage Load overvoltage Electronics/sensors undervoltage Load undervoltage
Diagnostics per internal communication	Module error Output short circuit/overload Short circuit/overload in sensor supply Undervoltage in load supply
Fieldbus interface	Ethernet
Field bus, protocol	PROFINET IRT PROFINET RT
Field bus, connection type	2x socket
Field bus, connection system	M12x1, D-coded to EN 61076-2-101
Field bus, connection pattern	4
Field bus interface, electrical isolation	yes
Field bus interface, transmission rate	100 Mbit/s
Max. address volume, inputs	1024 Byte
Max. address volume, outputs	1024 Byte
Configuration support	GSDML file
Communication interface, function	System communication XF20 OUT / XF21 OUT
Communication interface, connection type	2x socket
Communication interface, connection technology	M8x1, D-coded according to EN 61076-2-114
Communication interface, number of pins/wires	4
Communication interface, protocol	AP
Communication interface, shielding	yes
Power supply, function	Incoming electronics/sensors and load
Power supply, connection type	Plugs
power supply, connection system	M8x1, A-coded to EN 61076-2-104
Power supply, number of pins/wires	4
Power transmission, function	Outgoing electronics/sensors and load
Power transmission, connection type	Socket
Power transmission, connection technology	M8x1, A-coded to EN 61076-2-104
Power transmission, number of pins/wires	4
Note regarding operating voltage	SELV/PELV fixed power supplies required Note voltage drop
Nominal operating voltage DC of load	24 V
Permissible voltage fluctuation of load	± 25 %
Nominal DC operating voltage, electronics/sensors	24 V
Permissible voltage fluctuations for electronics/sensors	± 25%
Max. power supply	2 x 4 A (external fuse required)
Intrinsic current consumption at nominal operating voltage for electronics/sensors	Typically 80 mA
Intrinsic current consumption at nominal operating voltage load	Typically 5 mA
Power failure bridging	10 ms
Reverse polarity protection	yes