

# Compact cylinder ADN-S-20-5-A-P-A

Part number: 8091430

FESTO



## Data sheet

Feature	Value
Stroke	5 mm
Piston diameter	20 mm
Cushioning	Elastic cushioning rings/plates at both ends
Mounting position	optional
Mode of operation	Double-acting
Piston-rod end	Male thread
Design	Piston Piston rod
Position detection	Via proximity switch
Variants	Piston rod at one end
Operating pressure	0.06 MPa...1 MPa 0.6 bar...10 bar
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)
Corrosion resistance class CRC	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Cleanroom class	Class 6 according to ISO 14644-1
Ambient temperature	0 °C...60 °C
Impact energy in end positions	0.2 J
Theoretical force at 0.6 MPa (6 bar, 87 psi), return stroke	141 N
Theoretical force at 0.6 MPa (6 bar, 87 psi), advance stroke	188 N
Moving mass for 0 mm stroke	18 g
Additional moving mass per 10 mm stroke	6 g
Basic weight for 0 mm stroke	65 g
Additional weight per 10 mm stroke	26 g
Type of mounting	Either: With through-hole Via female thread With accessories
Pneumatic connection	M5
Note on materials	RoHS-compliant
Material cover	Anodised wrought aluminium alloy

<b>Feature</b>	<b>Value</b>
Material dynamic seals	NBR TPE-U(PU)
Material housing	Anodised wrought aluminium alloy
Material piston rod	High-alloy stainless steel