


# Sub-base VMPAL-AP-20-T135-RV

Part number: 8034564

FESTO



## Data sheet

Feature	Value
Construction width	20 mm
Width	21.2 mm
Length	107.3 mm
Grid dimension	21.2 mm
Pressure-zone division	Ducts 1, 3 and 5
Integrated function	Check valve
Max. number of valve positions	1
Flow direction	Non-reversible
Valve terminal structure	Valve sizes can be mixed
Operating pressure	-0.09 MPa...1 MPa -0.9 bar...10 bar
Pilot pressure	0.3 MPa...0.8 MPa 3 bar...8 bar
Suitability for vacuum	no
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)
Corrosion resistance class CRC	3 - high corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-5 °C...50 °C
Product weight	50 g
Pneumatic connection, port 2	For 18 mm cartridge
Pneumatic connection, port 4	For 18 mm cartridge
Note on materials	RoHS-compliant
Material sub-base	PA-reinforced