


Pressure sensor SPAN-P10R-M5F-PNLK-PNVBA-L1

Part number: 8035539

FESTO



Data sheet

Feature	Value
Approval	RCM trademark c UL us listed (OL)
CE mark (see declaration of conformity)	To EU EMC Directive In accordance with EU RoHS Directive
CE marking (see declaration of conformity)	To UK instructions for EMC To UK RoHS instructions
Certificate issuing authority	UL E322346
Note on materials	RoHS-compliant
Measured variable	Relative pressure
Measurement method	Piezoresistive pressure sensor
Start value for pressure measuring range	0 MPa 0 bar 0 psi
End value for pressure measuring range	1 MPa 10 bar 145 psi
Max. overload pressure	15 bar
Overload pressure	1.5 MPa 15 bar 217.5 psi
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4] Inert gases
Note on operating and pilot medium	Lubricated operation possible
Media temperature	0 °C...50 °C
Ambient temperature	0 °C...50 °C
Accuracy in ± % FS	1.5 %FS
Repetition accuracy in ± %FS	0.3 %FS
Temperature coefficient in ± %FS/K	0.05 %FS/K
Switching output	2 x PNP or 2 x NPN, switchable
Switching function	Window comparator Threshold value comparator Auto difference monitoring
Switching element function	N/C or N/O contact, switchable
Max. output current	100 mA

Feature	Value
Analogue output	0 - 10 V 4 - 20 mA 1 - 5 V
Max. load resistance current output	500 Ohm
Min. load resistance voltage output	20 kOhm
Short circuit current rating	yes
Protocol	IO-Link®
IO-Link, Protocol version	Device V 1.1
IO-Link, Profile	Smart sensor profile
IO-Link, Function classes	Binary data channel (BDC) Process data variable (PDV) Identification Diagnostics Teach channel
IO-Link, communication mode	COM2 (38.4 kBaud)
IO-Link, SIO-Mode support	Yes
IO-Link, Port class	A
IO-Link, Process data length OUT	0 bytes
IO-Link, Process data length IN	2 bytes
IO-Link, Process data content IN	14 bit PDV (pressure measurement value) 2 bit BDC (pressure monitoring)
IO-Link, Min. cycle time	3 ms
IO-Link, Data storage required	0,5 kB
Operational voltage range DC	15 V...30 V
Reverse polarity protection	For all electrical connections
Electrical connection 1, connection type	Plugs
Electrical connection 1, connector system	Connection pattern L1)
Electrical connection 1, number of connections/cores	4
Type of mounting	Front panel mounting Via wall/surface bracket
Mounting position	optional
Pneumatic connection	Female thread M5
Product weight	34 g
Material housing	PA-reinforced
Material in contact with the medium	FPM High-alloy stainless steel
Display type	Illuminated LCD
Displayable units	MPa bar inH2O inHg kPa kgf/cm ² mbar mmHg psi
Setting options	IO-Link® Teach-in Via display and keys
Protection against tampering	IO-Link PIN code
Setting range threshold value	0 %...100 %
Setting range hysteresis	0 %...90 %
Degree of protection	IP40
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L

Feature	Value
Suitability for the production of Li-ion batteries	Metals with more than 1% copper, zinc or nickel by mass are excluded from use. Exceptions are nickel in steel, chemically nickel-plated surfaces, printed circuit boards, cables, electrical plug connectors and coils
Cleanroom class	Class 4 according to ISO 14644-1