


# Compact cylinder AEN-S-50-25-A-P-A

Part number: 8092154

FESTO



## Data sheet

| Feature  | Value  |
|--|--|
| Stroke   | 25 mm  |
| Piston diameter  | 50 mm  |
| Cushioning   | Elastic cushioning rings/plates at both ends   |
| Mounting position  | optional   |
| Mode of operation  | Pushing  |
| Piston-rod end   | Male thread  |
| Design   | Piston<br>Piston rod   |
| Position detection   | Via proximity switch   |
| Variants   | Piston rod at one end  |
| Operating pressure   | 0.04 MPa...1 MPa<br>0.4 bar...10 bar   |
| Operating medium   | Compressed air to ISO 8573-1:2010 [7:4:4]  |
| Note on operating and pilot medium                           | Lubricated operation possible (in which case lubricated operation will always be required) |
| Corrosion resistance class CRC                               | 1 - Low corrosion stress   |
| LABS (PWIS) conformity                                       | VDMA24364-B2-L   |
| Ambient temperature  | 0 °C...60 °C   |
| Impact energy in end positions                               | 1 J  |
| Theoretical force at 0.6 MPa (6 bar, 87 psi), return stroke  | 71.5 N   |
| Theoretical force at 0.6 MPa (6 bar, 87 psi), advance stroke | 1106 N   |
| Moving mass for 0 mm stroke                                  | 104 g  |
| Additional moving mass per 10 mm stroke                      | 16 g   |
| Basic weight for 0 mm stroke                                 | 324 g  |
| Additional weight per 10 mm stroke                           | 63 g   |
| Type of mounting   | Either:<br>With through-hole<br>Via female thread<br>With accessories                      |
| Pneumatic connection   | G1/8   |
| Note on materials  | RoHS-compliant   |
| Material cover   | Anodised wrought aluminium alloy   |
| Material dynamic seals                                       | TPE-U(PU)  |

| Feature             | Value                            |
|---------------------|----------------------------------|
| Material housing    | Anodised wrought aluminium alloy |
| Material piston rod | High-alloy stainless steel       |