


parallel kit EAMM-U-30-V20-28AA-44

Part number: 8093176

FESTO



Data sheet

Feature	Value
Size	30
Centre-to-centre distance	44 mm
Assembly position	Any
Gear unit ratio	1:1
Max. speed	3,000 1/min
PWIS conformity	VDMA24364 zone III
Storage temperature	-20 ... 60 °C
Relative air humidity	0 - 95 %
Protection class	IP40
Ambient temperature	0 ... 50 °C
Mass moment of inertia	2.11 kgmm ²
No-load driving torque	0.015 Nm
Transferable torque	0.05 Nm
Product weight	94 g
Interface code, actuator	V20
Interface code, motor in	28AA
Materials note	Conforms to RoHS