


Mains filter CAMF-C6-F-C16-11A

Part number: 8096868

FESTO



Data sheet

Feature	Value
Short circuit current rating	no
Current rating at 40° C	16 A
Operational voltage range AC	0 V...520 V
Mains frequency	0 Hz...60 Hz
Insulation voltage	2650 V
Dimensions (W x L x H)	45 x 235 x 70 mm
Approval	ENEC UL - Recognized (OL) c UL - Recognized (OL)
CE mark (see declaration of conformity)	In accordance with EU RoHS Directive
LABS (PWIS) conformity	VDMA24364 zone III
Storage temperature	-25 °C...100 °C
Degree of protection	IP20
Ambient temperature	-25 °C...100 °C
Product weight	800 g
Type of mounting	Mounting plate, attached with screws
Note on materials	RoHS-compliant
Mounting position	Horizontal
Electrical connection 1, function	Power supply
Electrical connection 1, connection type	Terminal strip
Electrical connection 1, connector system	Screw terminal
Electrical connection 1, number of connections/cores	3
Electrical connection 1, used connections/cores	3
Electrical connection 1, conductor cross section	6 mm ² ...10 mm ²
Electrical connection 2, function	Power supply
Electrical connection 2, connection type	Terminal strip
Electrical connection 2, connector system	Screw terminal
Electrical connection 2, number of connections/cores	3
Electrical connection 2, used connections/cores	3
Electrical connection 2, conductor cross section	6 mm ² ...10 mm ²