

mini slide

EGSC-BS-KF-25-50-6P

Part number: 8048311

FESTO



Data sheet

Feature	Value
Working stroke	50 mm
Size	25
Stroke reserve	0 mm
Reversing backlash	150 µm
Spindle diameter	6 mm
Spindle pitch	6 mm/U
Assembly position	Any
Guide	Recirculating ball bearing guide
Design structure	Electric mini slide With ball screw
Motor type	Stepper motor Servomotor
Referencing	Fixed stop block positive Fixed stop block negative Reference switch
Spindle type	Ball screw
Position detection	For proximity sensor
Max. acceleration	15 m/s ²
Max. speed	0.4 m/s
Repetition accuracy	±0,015 mm
Duty cycle	100 %
Corrosion resistance classification CRC	0 - No corrosion stress
PWIS conformity	VDMA24364 zone III
RSBP classification to CD-0033	F1a
Cleanroom class	ISO class 9
Sound pressure level	50 dB(A)
Protection class	IP40
Ambient temperature	0 ... 50 °C
Fixed bearing dynamic basic load rating	2,810 N
Linear guide dynamic basic load rating	1,310 N
Ball screw drive dynamic basic load rating	1,700 N
Max. force F _y	669 N
Max. force F _z	669 N
Max. torque M _x	2 Nm
Max. torque M _y	2.1 Nm
Max. torque M _z	2.1 Nm
Max. radial force at drive shaft	30 N
Max. feed force F _x	20 N
Reference value for working load, horizontal	2 kg
Reference value for working load, vertical	2 kg
Ball screw drive statistical basic load rating	2,600 N
Linear guide statistical basic load rating	2,440 N
Mass moment of inertia J _H per metre of stroke	0.01507 kgcm ²
Mass moment of inertia J _L per kg of working load	0.00912 kgcm ²
Mass moment of inertia, J _O	0.00144 kgcm ²
Feed constant	6 mm/U

Feature	Value
Fixed bearing statistical basic load rating	1,340 N
Reference value, running performance	5,000 km
Maintenance interval	Life-time lubrication
Moving mass with 0 mm stroke	83 g
Additional mass factor per 10 mm of stroke	9 g
Product weight	269 g
Basic weight for 0 mm stroke	176 g
Additional weight per 10 mm stroke	19 g
Mounting type	with internal (female) thread with centring sleeve with accessories With cylindrical dowel pin
Interface code, actuator	V20
Materials note	Conforms to RoHS
Material guide slide	Roller bearing steel
Material guide rail	Roller bearing steel
Material housing	Anodised wrought aluminium alloy
Material yoke plate	Anodised wrought aluminium alloy
Material piston rod	High alloy steel, non-corrosive
Material slide	Anodised wrought aluminium alloy
Material spindle nut	Roller bearing steel
Material spindle	Roller bearing steel