


parallel kit EAMM-U-86-S48-60G-177

Part number: 8059009

FESTO

Suitable for electric drives.



Data sheet

Feature	Value
Size	86
Assembly position	Any
Max. speed	5,000 1/min
PWIS conformity	VDMA24364-B2-L
Storage temperature	-25 ... 60 °C
Relative air humidity	0 - 95 %
Protection class	IP40
Ambient temperature	-10 ... 60 °C
Mass moment of inertia	175 kgmm ²
No-load driving torque	0.25 Nm
Transferable torque	9.5 Nm
Product weight	3,300 g
Interface code, actuator	S48
Interface code, motor in	60G
Materials note	Conforms to RoHS