


Axial kit EAMM-A-L62-60H

Part number: 8063498

FESTO



Data sheet

Feature	Value
Mounting position	optional
LABS (PWIS) conformity	VDMA24364-B2-L
Storage temperature	-25 °C...60 °C
Relative air humidity	0 - 95%
Degree of protection	IP40
Ambient temperature	-10 °C...60 °C
Transmittable torque	38 Nm
Product weight	961 g
Interface code, actuator	L62
Interface code, motor in	60H
Note on materials	RoHS-compliant