

Round cylinder CRDSNU-B-40-10-PPS-A-MG-A1

Part number: 8073989

FESTO



Data sheet

Feature	Value
Stroke	10 mm
Piston diameter	40 mm
Based on standard	ISO 15552
Cushioning	Self-adjusting pneumatic end-position cushioning
Mounting position	optional
Design	Piston Piston rod Cylinder barrel
Position detection	Via proximity switch
Operating pressure	0.1 MPa...1 MPa 1 bar...10 bar
Mode of operation	Double-acting
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)
Corrosion resistance class CRC	4 - Very high corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Suitable for use with food	See supplementary material information
Ambient temperature	0 °C...80 °C
Theoretical force at 0.6 MPa (6 bar, 87 psi), return stroke	633 N
Theoretical force at 0.6 MPa (6 bar, 87 psi), advance stroke	754 N
Moving mass for 0 mm stroke	232 g
Additional moving mass per 10 mm stroke	15.8 g
Basic weight for 0 mm stroke	1327 g
Additional weight per 10 mm stroke	23.8 g
Type of mounting	With accessories
Pneumatic connection	G1/4
Note on materials	RoHS-compliant
Material cover	High-alloy stainless steel
Material piston rod	High-alloy stainless steel
Material cylinder barrel	High-alloy stainless steel