

Parallel gripper DHPC-6-A-S

Part number: 8116735

FESTO



Data sheet

Feature	Value
Size	6
Stroke per gripper jaws	2 mm
Max. replacement accuracy	0.2 mm
Max. angular gripper jaw backlash ax, ay	0 deg
Max. gripper jaw backlash Sz	0 mm
Rotationally symmetrical	0.2 mm
Repetition accuracy, gripper	0.02 mm
Number of gripper jaws	2
Drive system	Pneumatic
Mounting position	optional
Mode of operation	Double-acting
Gripper function	Parallel
Gripper force back-up	None
Design	Connection direction at side Lever Standard mounting method for gripper fingers Force pilot operated motion sequence
Guide	Ball guide
Position detection	Via proximity switch
Variants	Metals with copper, zinc or nickel as main constituent are excluded from use. Exceptions are nickel in steel, chemically nickel-plated surfaces, printed circuit boards, cables, electrical plug connectors and coils.
Total gripping force, opening, 0.6MPa (6bar, 87 psi)	14.6 N
Total gripping force, closing, 0.6MPa (6bar, 87 psi)	11 N
Operating pressure	0.15 MPa...0.8 MPa 1.5 bar...8 bar 21.75 psi...116 psi
Max. operating frequency of gripper	3 Hz
Min. opening time at 0.6 MPa (6 bar, 87 psi)	9 ms
Min. closing time at 0.6 MPa (6 bar, 87 psi)	11 ms
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)
Corrosion resistance class CRC	0 - No corrosion stress

Feature	Value
LABS (PWIS) conformity	VDMA24364-B2-L
Suitability for the production of Li-ion batteries	Metals with more than 1% copper, zinc or nickel by mass are excluded from use. Exceptions are nickel in steel, chemically nickel-plated surfaces, printed circuit boards, cables, electrical plug connectors and coils
Ambient temperature	-10 °C...60 °C
Gripper force per gripper jaw, opening, 0.6 MPa (6 bar, 87 psi)	7.3 N
Gripper force per gripper jaw, closing, 0.6 MPa (6 bar, 87 psi)	5.5 N
Mass moment of inertia	0.011 kgcm ²
Max. force on gripper jaw Fz static	5 N
Max. torque at gripper Mx static	0.02 Nm
Max. torque at gripper My static	0.04 Nm
Max. torque at gripper Mz static	0.02 Nm
Product weight	25 g
Type of mounting	Either: Direct mounting via through-hole Direct mounting via thread
Pneumatic connection	M3
Note on materials	RoHS-compliant
Material housing	Anodised aluminium
Material gripper jaws	High-alloy stainless steel