

Radial gripper DHRC-6-A

Part number: 8125285

FESTO



Data sheet

Feature	Value
Size	6
Max. replacement accuracy	0.2 mm
Max. opening angle	180 deg
Repetition accuracy, gripper	0.1 mm
Number of gripper jaws	2
Drive system	Pneumatic
Mounting position	optional
Mode of operation	Double-acting
Gripper function	Radial
Gripper force back-up	None
Design	Connection direction at side Force pilot operated motion sequence
Position detection	Via proximity switch
Operating pressure	0.25 MPa...0.8 MPa 2.5 bar...8 bar 36.25 psi...116 psi
Max. operating frequency of gripper	3 Hz
Min. opening time at 0.6 MPa (6 bar, 87 psi)	10 ms
Min. closing time at 0.6 MPa (6 bar, 87 psi)	19 ms
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)
Corrosion resistance class CRC	0 - No corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Ambient temperature	-10 °C...60 °C
Total gripping torque at 0.6 MPa (6 bar, 87 psi), opening	6.7 Ncm
Total gripper torque, closing, 0.6 MPa (6 bar, 87 psi)	4.8 Ncm
Mass moment of inertia	0.01 kgcm ²
Max. force on gripper jaw Fz static	12 N
Max. torque at gripper Mx static	0.3 Nm
Max. torque at gripper My static	0.3 Nm
Max. torque at gripper Mz static	0.3 Nm

Feature	Value
Product weight	24.5 g
Type of mounting	Either: Direct mounting via through-hole Direct mounting via thread
Pneumatic connection	M3
Note on materials	RoHS-compliant
Material cover cap	Wrought aluminium alloy, anodised
Material housing	Anodised wrought aluminium alloy
Material gripper jaws	High-alloy steel