

# Blanking plug B-M5-F1A

Part number: 8142288

FESTO



## Data sheet

Feature	Value
Size of pack	10
Variants	Metals with copper, zinc or nickel as main constituent are excluded from use. Exceptions are nickel in steel, chemically nickel-plated surfaces, printed circuit boards, cables, electrical plug connectors and coils.
LABS (PWIS) conformity	VDMA24364-B2-L
Suitability for the production of Li-ion batteries	Metals with more than 1% copper, zinc or nickel by mass are excluded from use. Exceptions are nickel in steel, chemically nickel-plated surfaces, printed circuit boards, cables, electrical plug connectors and coils
Cleanroom class	Class 6 according to ISO 14644-1
Nominal torque	1.5 Nm
Tolerance for nominal tightening torque	-30%
Product weight	1 g
Type of mounting	Internal hexagon, size 2.5 mm
Pneumatic connection, port 1	Male thread M5
Note on materials	RoHS-compliant
Material blanking plug	Steel, nickel-plated
Material o-ring	Stainless steel NBR