



toothed belt axis ELGR-TB-35-400-0H

Part number: 8083773

FESTO



Data sheet

Feature	Value
Effective diameter of drive pinion	18.46 mm
Working stroke	400 mm
Size	35
Toothed-belt stretch	0.094 %
Toothed-belt pitch	2 mm
Assembly position	Any
Guide	Recirculating ball bearing guide
Design structure	Electromechanical linear axis With toothed belt
Motor type	Stepper motor Servomotor
Max. acceleration	50 m/s ²
Max. speed	0.9 ... 3 m/s
Repetition accuracy	±0,1 mm
Duty cycle	100 %
PWIS conformity	VDMA24364 zone III
Protection class	IP20
Ambient temperature	-10 ... 50 °C
Area moment of inertia 2nd degree Iy	3.77E+03 mm ⁴
Area moment of inertia 2nd degree Iz	4.19E+03 mm ⁴
Max. drive torque	0.46 Nm
Max. force Fy	50 N
Max. force Fz	50 N
Max. idling displacement resistance	10.8 N
Max. feed force Fx	50 N
No-load driving torque	0.1 Nm
Mass moment of inertia JH per metre of stroke	0.026 kgcm ²
Mass moment of inertia JL per kg of working load	0.85 kgcm ²
Feed constant	58 mm/U
Reference value, running performance	5,000 km
Additional mass factor per 10 mm of stroke	0.31 g
Product weight	2,470 g
Additional weight per 10 mm stroke	25 g
Material of profile	Wrought Aluminium alloy Anodised
Materials note	Conforms to RoHS
Material drive cover	Wrought Aluminium alloy Anodised
Material pulleys	High alloy steel, non-corrosive
Material slide	Wrought Aluminium alloy Anodised
Material toothed belt clamping piece	Beryllium bronze
Material toothed belt	polychloroprene with glass cord and nylon coating