

# Mini slide DGST-20-30-PA

Part number: 8085141

FESTO



## Data sheet

Feature	Value
Stroke	30 mm
Adjustable end position range/length front	30.1 mm
Adjustable end position range/length rear	30.1 mm
Piston diameter	20 mm
Operating mode, drive unit	Yoke
Cushioning	Elastic cushioning rings/plates at both ends
Mounting position	optional
Guide	Ball bearing cage guide
Design	Twin piston Yoke Piston rod Slide
Position detection	Via proximity switch
Operating pressure	0.1 MPa...0.8 MPa 1 bar...8 bar 14.5 psi...116 psi
Max. speed	0.8 m/s
Repetition accuracy	≤ 0.3 mm
Mode of operation	Double-acting
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)
Corrosion resistance class CRC	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-10 °C...60 °C
Impact energy in end positions	0.35 J
Cushioning length	1.2 mm
Max. force F <sub>y</sub>	1110 N
Max. force F <sub>z</sub>	1110 N
Max. moment M <sub>x</sub>	11 Nm
Max. moment M <sub>y</sub>	12 Nm
Max. moment M <sub>z</sub>	12 Nm

<b>Feature</b>	<b>Value</b>
Theoretical force at 0.6 MPa (6 bar, 87 psi), return stroke	317 N
Theoretical force at 0.6 MPa (6 bar, 87 psi), advance stroke	377 N
Moving mass	527.5 g
Product weight	1139 g
Type of mounting	With through-hole
Pneumatic connection	G1/8
Note on materials	RoHS-compliant
Material cover	Wrought aluminium alloy
Material seals	HNBR
Material guide	POM TPE-E High-alloy steel
Material housing	Wrought aluminium alloy
Material piston rod	High-alloy stainless steel