

mini slide

DGST-25-50-Y12A

Part number: 8085193

FESTO



Data sheet

| Feature | Value |
|--|---|
| Stroke | 50 mm |
| Adjustable endposition range/front length | 32 mm |
| Adjustable endposition range/rear length | 30.4 mm |
| Piston diameter | 25 mm |
| Operating mode of drive unit | Yoke |
| Cushioning | Y12: external hydraulic cushioning |
| Assembly position | Any |
| Guide | Ball bearing cage guide |
| Design structure | twin piston Yoke Piston rod Slide |
| Position detection | For proximity sensor |
| Operating pressure MPa | 0.1 ... 0.8 MPa |
| Operating pressure | 1 ... 8 bar 14.5 ... 116 psi |
| Max. speed | 0.8 m/s |
| Repetition accuracy | ≤ 0,02 mm |
| Mode of operation | double-acting |
| Operating medium | Compressed air in accordance with ISO8573-1:2010 [7:4:4] |
| Note on operating and pilot medium | Lubricated operation possible (subsequently required for further operation) |
| Corrosion resistance classification CRC | 1 - Low corrosion stress |
| PWIS conformity | VDMA24364-B1/B2-L |
| Ambient temperature | -10 ... 60 °C |
| Impact energy in end positions | 6 J |
| Cushioning length | 10 mm |
| Max. force F _y | 1,080 N |
| Max. force F _z | 1,080 N |
| Max. torque M _x | 12 Nm |
| Max. torque M _y | 11 Nm |
| Max. torque M _z | 11 Nm |
| Theoretical force at 0.6 MPa (6 bar, 87 psi), retracting | 495 N |
| Theoretical force at 0.6 MPa (6 bar, 87 psi), advance | 589 N |
| Moving mass | 1,002 g |
| Product weight | 2,026 g |
| Mounting type | with through hole |
| Pneumatic connection | G1/8 |
| Materials note | Conforms to RoHS |
| Material cover | Wrought Aluminium alloy |
| Material seals | HNBR |
| Material of guide | POM High alloy steel TPE-E |
| Material housing | Wrought Aluminium alloy |
| Material piston rod | High alloy steel, non-corrosive |