

Bus node CTEU-VN

Part number: 8087559

FESTO



Data sheet

Feature	Value
Dimensions (W x L x H)	40 x 91 x 50 mm
Grid dimension	40 mm
Type of mounting	On electrical interface On electrical sub-base
Product weight	98 g
Ambient temperature	-5 °C...50 °C
Storage temperature	-20 °C...70 °C
Degree of protection	IP65 IP67
Note on degree of protection	In assembled state Unused connections sealed
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364 zone III
CE mark (see declaration of conformity)	To EU EMC Directive In accordance with EU RoHS Directive
CE marking (see declaration of conformity)	To UK instructions for EMC To UK RoHS instructions
KC mark	KC-EMV
Approval	RCM trademark
Note on materials	RoHS-compliant
Material housing	PA
LED display, product-specific	PS: Operating voltage for electronics and load supply X1: System status of module at I-Port 1 X2: System status of module at I-Port 2
LED display, bus-specific	XF1 AC: network data exchange, port 1 XF1 LI: network active, port 1
Diagnosis	Communication fault System diagnostics Undervoltage
Fieldbus interface	Ethernet
Field bus, protocol	VARAN
Field bus, connection type	2x socket
Field bus, connection system	M12x1, D-coded to EN 61076-2-101
Field bus, connection pattern	4

Feature	Value
Field bus interface, electrical isolation	yes
Field bus interface, transmission rate	100 Mbit/s
Max. address volume, inputs	32 Byte
Max. address volume, outputs	32 Byte
Parameterisation	Fail-safe response IO-Link mode
Internal cycle time	1 ms per 1 byte of user data
Configuration support	LASAL module
Additional functions	FFT VARAN splitter
Power supply, function	Electronics and load
Power supply, connection type	Plugs
power supply, connection system	M12x1, A-coded according to EN 61076-2-101
Power supply, number of pins/wires	5
Operational voltage range DC	18 V...30 V
Nominal operating voltage DC	24 V
Max. power supply	4 A
Intern power consumption nominal operating voltage	Typ. 65 mA