

ball valve

VZBE-4-WA-63-T-2-F1012-V15V15

Part number: 8089048

FESTO

Festo is only a retailer of this product, not the manufacturer.



Data sheet

| Feature | Value |
|---|---|
| Design structure | 2-way ball valve |
| Type of actuation | mechanical |
| Sealing principle | soft |
| Assembly position | Any |
| Mounting type | Line installation |
| Process valve connection | Weld-on end to ASME B16.11 |
| Switching position indicator | Slot direction = flow direction |
| Flange hole pattern | F10 F12 |
| Inside diameter | 96 mm |
| Nominal diameter DN | 100 |
| Valve function | 2/2 |
| Flow direction | reversible |
| Nominal pressure of process valve | 63 |
| Breakaway torque at differential pressure, nominal pressure, process valve PN | 170 Nm |
| Based on the standard | ASME B16.11 ISO 5211 |
| Medium | Vapour Compressed air in accordance with ISO8573-1:2010 [-:~:] Inert gases Water Neutral fluids |
| Medium temperature | -20 ... 200 °C |
| Flow rate Kv | 1,637 m3/h |
| Materials note | Conforms to RoHS |
| PWIS conformity | VDMA24364 zone III |
| Material housing | Stainless steel casting |
| Material number for housing | 1.4408/CF8M |
| Material seat seal | PTFE, modified |
| Material seals | FPM PTFE |
| Material ball | Stainless steel casting |
| Material number for ball | 1.4408/CF8M |
| Material shaft | High alloy steel, non-corrosive |
| Material number for shaft | 1.4401 |
| Product weight | 18,900 g |
| Authorisation | CRN |
| CE mark (see declaration of conformity) | to EU directive pressure devices |
| Corrosion resistance classification CRC | 4 - Very high corrosion stress |