

# Standards-based cylinder DSBC-40-500-D3-PPVA-N3

Part number: 8165584

FESTO



## Data sheet

| Feature                                                      | Value                                                                                      |
|--------------------------------------------------------------|--------------------------------------------------------------------------------------------|
| Stroke                                                       | 500 mm                                                                                     |
| Piston diameter                                              | 40 mm                                                                                      |
| Piston rod thread                                            | M12x1.25                                                                                   |
| Cushioning                                                   | Pneumatic cushioning, adjustable at both ends                                              |
| Mounting position                                            | optional                                                                                   |
| Conforms to standard                                         | ISO 15552                                                                                  |
| Piston-rod end                                               | Male thread                                                                                |
| Design                                                       | Piston<br>Piston rod<br>Profile barrel                                                     |
| Position detection                                           | Via proximity switch                                                                       |
| Variants                                                     | Piston rod at one end                                                                      |
| Operating pressure                                           | 0.06 MPa...1.2 MPa<br>0.6 bar...12 bar                                                     |
| Mode of operation                                            | Double-acting                                                                              |
| Operating medium                                             | Compressed air to ISO 8573-1:2010 [7:4:4]                                                  |
| Note on operating and pilot medium                           | Lubricated operation possible (in which case lubricated operation will always be required) |
| Corrosion resistance class CRC                               | 2 - Moderate corrosion stress                                                              |
| LABS (PWIS) conformity                                       | VDMA24364-B1/B2-L                                                                          |
| Ambient temperature                                          | -20 °C...80 °C                                                                             |
| Impact energy in end positions                               | 0.7 J                                                                                      |
| Cushioning length                                            | 19 mm                                                                                      |
| Theoretical force at 0.6 MPa (6 bar, 87 psi), return stroke  | 633 N                                                                                      |
| Theoretical force at 0.6 MPa (6 bar, 87 psi), advance stroke | 754 N                                                                                      |
| Moving mass for 0 mm stroke                                  | 205 g                                                                                      |
| Additional moving mass per 10 mm stroke                      | 16 g                                                                                       |
| Basic weight for 0 mm stroke                                 | 768 g                                                                                      |
| Additional weight per 10 mm stroke                           | 49 g                                                                                       |
| Type of mounting                                             | Either:<br>Via female thread<br>With accessories                                           |
| Pneumatic connection                                         | G1/4                                                                                       |

| <b>Feature</b>             | <b>Value</b>                            |
|----------------------------|-----------------------------------------|
| Note on materials          | RoHS-compliant                          |
| Material cover             | Die-cast aluminium, coated              |
| Material piston seal       | TPE-U(PU)                               |
| Material piston            | Wrought aluminium alloy                 |
| Material piston rod        | High-alloy steel                        |
| Material piston rod wiper  | TPE-U(PU)                               |
| Buffer seal material       | TPE-U(PU)                               |
| Cushioning piston material | POM                                     |
| Material cylinder barrel   | Smooth-anodised wrought aluminium alloy |
| Material nut               | Galvanised steel                        |
| Material rod wiper         | TPE-E                                   |
| Material bearing           | Metal polymer compound                  |
| Material collar screws     | Galvanised steel                        |