


Connecting cable NEBC-D8W4-ES-0.5-N-S-D8W4-ET-G2

Part number: 8176606

FESTO



Data sheet

Feature	Value
Based on standard	EN 61076-2-114
Cable designation	Without inscription label holder
Frequency of connection	100
Product weight	46 g
Electrical connection 1, function	Controller side
Electrical connection 1, design	Round
Electrical connection 1, connection type	Plugs
Electrical connection 1, cable outlet	Angled
Electrical connection 1, connector system	M8x1, D-coded according to EN 61076-2-114
Electrical connection 1, number of connections/cores	4
Electrical connection 1, used connections/cores	4
Electrical connection 1, type of mounting	Screw-type lock with longitudinal knurl
Electrical connection 2, function	Controller side
Electrical connection 2, design	Round
Electrical connection 2, connection type	Plugs
Electrical connection 2, cable outlet	Angled
Electrical connection 2, connector system	M8x1, D-coded according to EN 61076-2-114
Electrical connection 2, number of connections/cores	4
Electrical connection 2, used connections/cores	4
electrical connection 2, type of mounting	Screw-type lock with longitudinal knurl
Operational voltage range DC	0 V...30 V
Nominal operating voltage DC	24 V
Current rating at 40° C	3 A
Immunity to surge	1.5 kV
Reverse polarity protection	no
Protective conductor connection	Not available
Shielding	yes
Transmission characteristics	According to system communication AP
Cable length	0.5 m
Cable characteristic	Suitable for energy chains
Test conditions cable	Test conditions on request

Feature	Value
Bending radius, fixed cable	20 mm
Bending radius, moving cable	75 mm
Cable diameter	6.3 mm
Cable diameter tolerance	± 0.2 mm
Cable structure	1 x (4 x AWG22)
Conductor nominal cross section	AWG22
Degree of protection	IP65 IP67
Note on degree of protection	In assembled state
Special characteristics	Oil resistant
Ambient temperature	-20 °C...60 °C
Ambient temperature with moving cable	-5 °C...60 °C
Storage temperature	-40 °C...70 °C
CE mark (see declaration of conformity)	In accordance with EU RoHS Directive
CE marking (see declaration of conformity)	To UK RoHS instructions
LABS (PWIS) conformity	VDMA24364-B2-L
Note on materials	RoHS-compliant Free of halogen
Pollution degree	3
Corrosion resistance class CRC	2 - Moderate corrosion stress
Material cable sheath	TPE-U(PUR)
Cable sheath colour	Silver-grey with sky blue stripe
Material housing	PA TPE-U(PUR)
Housing colour	Black
Material screw-type lock	Nickel-plated brass
Material seals	NBR
Material electrical contact	Gold-plated copper alloy
Material insulating sheath	PP