

# Dosing needle set VAVN-N-A1.6-03-30-F-V-V1-P10

Part number: 8104295

FESTO



## Data sheet

Feature	Value
Size of pack	10
Outside diameter dosing needle	1.6 mm
Length of dosing needle	30 mm
Nominal width of dosing needle	0.3 mm
Design of dosing needle	with chamfer with tapering
Corrosion resistance class CRC	3 - high corrosion stress
LABS (PWIS) conformity	VDMA24364 zone III
Suitable for use with food	See supplementary material information
Fluid connection	Terminal connection
Medium	Liquid media Gaseous media
Note on the medium	Observe resistance of materials that come into contact with the media Maximum particle size 5 µm
Operating pressure	0 MPa...0.4 MPa 0 bar...4 bar
Standard nominal flow rate	1.37 l/min
Note on standard nominal flow rate	At pressure drop from 1 -> 0 bar (gaseous media)
Flow rate Kv	0.003 m <sup>3</sup> /h
Note on flow rate Kv	For medium water
Media temperature	5 °C...60 °C
Ambient temperature	5 °C...60 °C
Storage temperature	-20 °C...70 °C
Mounting position	optional
Product weight	3.9 g
Note on materials	RoHS-compliant
Material of dosing needle	High-alloy stainless steel
Material number of dosing needle	1.4404
Material in contact with the medium	High-alloy stainless steel