



Linear actuator DGO-12- -P-A-B

Part number: 15221

FESTO

For proximity sensing, with magnetic coupling.



Data sheet

Feature	Value
Stroke	10 ... 1,200 mm
Piston diameter	12 mm
Cushioning	P: Flexible cushioning rings/plates at both ends
Assembly position	Any
Driver principle	force-locking (magnet)
Position detection	For proximity sensor
Working pressure	2 ... 7 bar
Mode of operation	double-acting
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:-:-]
Note on operating and pilot medium	Lubricated operation possible (subsequently required for further operation)
PWIS conformity	VDMA24364-B2-L
Ambient temperature	-20 ... 60 °C
Theoretical force at 0.6 MPa (6 bar, 87 psi), retracting	68 N
Theoretical force at 0.6 MPa (6 bar, 87 psi), advance	68 N
Additional mass factor per 10 mm of stroke	2 g
Basic weight for 0 mm stroke	320 g
Pneumatic connection	M5
Material cover	Aluminum
Material seals	NBR TPE-U(PU)
Material housing	High alloy steel