

servo motor EMMT-AS-150-LKR-HS-R3SB

Part number: 8148363

FESTO



Data sheet

Feature	Value
Ambient temperature	-15 ... 40 °C
Note on ambient temperature	up to 80°C with derating -1.5%/°C
Max. installation height	4,000 m
Note on max. installation height	As of 1,000 m, only with derating of -1.0% per 100 m
Storage temperature	-20 ... 70 °C
Relative air humidity	0 - 90 %
Conforms to standard	IEC 60034
Thermal class according to EN 60034-1	F
Max. winding temperature	155 °C
Rating class according to EN 60034-1	S1
Temperature monitoring	Digital motor temperature transmission via EnDat® 2.2
Motor type to EN 60034-7	IM B5 IM V1 IM V3
Assembly position	Any
Protection class	IP21
Note on degree of protection	IP21 for motor shaft without rotary shaft seal IP65 motor shaft with RWDR IP67 for motor housing with connection technology
Concentricity, coaxiality, axial runout to DIN SPEC 42955	N
Balance quality	G 2,5
Detent torque	<1.0% of peak torque
Storage lifetime under nominal conditions	20,000 h
Shaft design Featherkey	DIN 6885 A 8 x 7 x 36
Interface code, motor out	150A
Electrical connection 1, connection type	Hybrid plugs
Electrical connection 1, connection technology	M40x1
Electrical connection 1, number of pins/wires	15
Degree of contamination	2
Materials note	Conforms to RoHS
Corrosion resistance classification CRC	0 - No corrosion stress
PWIS conformity	VDMA24364 zone III
Vibration resistance	as per EN 60068-2-6
Shock resistance	as per EN 60068-2-29 15 g/11 ms to EN 60068-2-27
Authorisation	RCM Mark c UL us - Recognized (OL)
CE mark (see declaration of conformity)	to EU directive for EMC to EU directive low-voltage devices in accordance with EU RoHS directive
UKCA marking (see declaration of conformity)	To UK instructions for electrical equipment To UK instructions for EMC To UK RoHS instructions
Certificate issuing department	UL E342973
Nominal operating voltage DC	680 V

Feature	Value
Type of winding switch	Star inside
Number of pole pairs	5
Standstill torque	45.5 Nm
Nominal torque	29 Nm
Peak torque	87 Nm
Nominal rotary speed	2,100 1/min
Max. speed	3,495 1/min
Max. mechanical speed	8,000 1/min
Nominal motor power	6,377 W
Continuous open-circuit current	23.6 A
Nominal motor current	15.4 A
Peak current	49.5 A
Motor constant	1.88 Nm/A
Standstill torque constant	2.23 Nm/A
Voltage constant, phase-to-phase	135.1 mVmin
Phase-phase winding resistance	0.25 Ohm
Phase-phase winding inductance	4.4 mH
Winding longitudinal inductivity Ld (phase)	2.15 mH
Winding cross inductivity Lq (phase)	2.2 mH
Electric time constant	17.1 ms
Thermal time constant	55 min
Thermal resistance	0.39 K/W
Measuring flange	450 x 450 x 30, steel
Overall mass moment of inertia at power take-off	70.1 kgcm ²
Product weight	29,700 g
Permissible axial shaft load	274 N
Permissible radial shaft load	1,370 N
Rotor position sensor	Absolute single turn encoder
Rotor position sensor, manufacturer designation	ECl 1319
Rotor position sensor, absolute detectable revolutions	1
Rotary position encoder interface	EnDat 22
Rotary position encoder measuring principle	Inductive
Rotor position sensor, DC operating voltage	5 V
Rotor position sensor, DC operating voltage range	3.6 ... 14 V
Rotor position sensor, position values per revolution	524,288
Rotor position encoder resolution	19 Bit
Rotor position sensor, system accuracy of angle measurement	-65 ... 65 arcsec
Brake holding torque	65 Nm
Operating voltage DC for brake	24 V
Brake current consumption	1.08 A
Power consumption, brake	26 W
Brake separation time	200 ms
Brake closing time	40 ms
DC brake response delay	10 ms
Max. brake no-load speed	8,000 1/min
Mass moment of inertia of brake	12.5 kgcm ²
Switching cycles, holding brake	5 million idle actuations (without work of friction!)
MTTF, subcomponent	190 years, rotor position sensor
Energy efficiency	ENEFF (CN) / Class 1