


Angle gripper DHWS-40-A

Part number: 1310184

FESTO



Data sheet

Feature	Value
Size	40
Max. replacement accuracy	≤ 0.2 mm
Max. opening angle	40 deg
Rotationally symmetrical	≤ 0.2 mm
Repetition accuracy, gripper	≤ 0.04 mm
Number of gripper fingers	2
Assembly position	Any
Mode of operation	double-acting
Gripper function	Angle
Design structure	Lever
Position detection	For proximity sensor
Working pressure	2 ... 8 bar
Max. operating frequency of gripper	≤ 3 Hz
Min. opening time at 0.6 MPa (6 bar, 87 psi)	63 ms
Min. closing time at 0.6 MPa (6 bar, 87 psi)	96 ms
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (subsequently required for further operation)
Corrosion resistance classification CRC	1 - Low corrosion stress
PWIS conformity	VDMA24364-B2-L
RSBP classification to CD-0033	F5
Ambient temperature	5 ... 60 °C
Total gripping torque at 0.6 MPa (6 bar, 87 psi) opening	1,497 Ncm
Total gripping torque at 0.6 MPa (6 bar, 87 psi) closing	1,362 Ncm
Mass moment of inertia	3.81 kgcm ²
Max. force on gripper jaw Fz static	200 N
Max. torque at gripper Mx static	13 Nm
Max. torque at gripper My static	13 Nm
Max. torque at gripper Mz static	13 Nm
Product weight	775 g
Mounting type	Internal thread and centering sleeve With through-hole and centering sleeve Optional
Pneumatic connection	G1/8
Materials note	Conforms to RoHS
Material cover cap	PA
Material housing	Wrought Aluminum alloy Hard anodized
Material gripper jaws	High alloy steel